




- IMAGE & DIMENSIONS ARE USING A 4" X 4" PAD
- ADDITIONAL LATERAL RANGE CAN BE ACHIEVED USING TALLER PADS

USABLE LATERAL RANGES

LATERAL RANGE - POS(PA): MEASURED FROM BOTTOM OF SHELL						
	LT		MT		UT	SH
	(M)	(T)	(S)	(T)	(M)	(S)
HIGHEST	9.9"	10.9"	12.7"	13.7"	14.9"	15.9"
LOWEST	5.6"	5.8"	6.1"	7.1"	7.1"	7.1"
RANGE	4.3"	5.1"	6.6"	6.6"	7.8"	8.8"



LATERAL RANGE - POS(PA): MEASURED FROM BOTTOM OF SHELL												
	LT			MT			UT			SH		
	(S)	(M)	(T)	(S)	(M)	(T)	(S)	(M)	(T)	(S)	(M)	(T)
HIGHEST	8.6"	10.0"	11.0"	12.8"	13.3"	14.7"	15.5"	16.6"	17.7"	16.0"	16.8"	18.0"
LOWEST	-0.4	-0.4"	-0.4"	-0.2"	0.3"	-1.3"	-0.8"	-0.7"	-0.6"	-0.3"	-0.2"	0.3"
RANGE	9.0"	10.4"	11.4"	13.0"	13.0"	16.0"	16.3"	17.3"	18.3"	16.3"	17.0"	17.7"



LATERAL RANGE - POSTERIOR LATERAL(PL): MEASURED FROM BOTTOM OF SHELL									
	MT			UT			SH		
	(S)	(M)	(T)	(S)	(M)	(T)	(S)	(M)	(T)
HIGHEST	12.8"	13.6"	15.0"	15.5"	16.6"	17.7"	16.0"	16.8"	18.0"
LOWEST	-0.2"	0.3"	-1.3"	-0.8"	-0.7"	-0.6"	-0.3"	-0.2"	0.3"
LATERAL RANGE	13.0"	13.3"	16.3"	16.3"	17.3"	18.3"	16.3"	17.0"	17.7"